## Broom, 610 mm, Soft/hard, Yellow







Designed for the effective cleaning of both wet and dry surfaces, this Broom has firm front bristles that loosen stubborn dirt and heavier debris, while the softer rear bristles gather the finer particles.

## **Technical Data**

Item Number	31946
Bristle stiffness	Soft/hard
Visible bristle length	60 mm
Material	Polypropylene Polyester (PBT) Stainless Steel (AISI 304)
Complies with (EC) 1935/2004 on food contact materials <sup>1</sup>	Yes
Complies with EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
Complies with FDA RegulationI CFR 21 <sup>1</sup>	Yes
Complies with UK 2019 No. 704 on food contact materials	Yes
Complies with REACH Regulation (EC) No. 1907/2006	Yes
Complies with California Proposition 65	Yes
Complies with Halal and Kosher	Yes
PFAS, Phthalates and BPA intentionally added	No
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 180-200 cm)	240 Pcs.
Quantity Per Layer (Pallet)	40 Pcs.
Box Length	610 mm
Box Width	290 mm
Box Height	200 mm
Length/Depth	610 mm
Width	70 mm
Height	125 mm
Net Weight	0.75 kg
Weight bag (Recycling Symbol "4" Low Density Polyethylene (LDPE))	0.0147 kg
Weight cardboard (Recycling symbol "20" PAP)	0.0253 kg
Tare total	0.04 kg
Gross Weight	0.79 kg
Cubic metre	0.005338 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature <sup>3</sup>	-20 °C
Max. drying temperature	100 °C
Min. pH-value in usage concentration	2 pH

Max. pH-value in Usage Concentration	10.5 pH
GTIN-13 Number	5705020319464
GTIN-14 Number (Box quantity)	15705020319461
Customs Tariff No.	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

3. Do not store the product below 0° Celsius.